



Representative

Catalog Number: H125TBF
Product ID: 7TBD013080R0012
UPC Number: 78621000299
Status: A

1-1/4 Inch Zinc Thru Bulkhead Fitting for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Thru Bulkhead Fitting
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Trade Size	1-1/4 in
Outside Diameter	2-3/8 in
Material	Zinc

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

Packaging

Inner Quantity	5
Inner Dimensions (inches)	5.1x4.25x6.4
Outer Quantity	10
Outer Dimensions (inches)	10.8x6.7x5.25
Weight Uom	88 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------