




Actual



Representative

**Catalog Number:** H150GRSST  
**Product ID:** 7TBD013740R0003  
**UPC Number:** 78621000282  
**EAN Number:** 05415022256956  
**Status:** A

1-1/2 Inch 316 Stainless Steel Grounding Hub, Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a)
- Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.
- Meets NEMA sealing requirements for NEMA 3R, 4, 4X and 13 enclosures

#### North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Grounding Hub
Special Features	Hexagonal/Splined Body and Locknut Enable Fast and Easy Installation
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Trade Size	1-1/2 in
Outside Diameter	2.75 in
Length	1.88 in
Material	316 Stainless Steel

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Stainless steel

#### Packaging

Inner Quantity	1
Inner Dimensions (inches)	2.5x2.5x2
Outer Quantity	10
Outer Dimensions (inches)	21.5x4.3x3.5
Weight Uom	91.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------