



Representative

**Catalog Number:** H200BHDA  
**Product ID:** 7TBD013080R0020  
**UPC Number:** 78621000334  
**Status:** A

2 Inch Aluminum, Bulkhead Fittings with Insulating Throat Thermoplastic, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

### North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Bulkhead Fitting
Special Features	Thermoplastic Insulating Throat with Rating up to 105 Degree Celsius
Application	A Fitting for Connecting a Junction Box to a Conduit System
Standard	UL E23018, CSA
Trade Size	2 in
Outside Diameter	3-1/4 in
Material	Aluminum

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

### Packaging

Outer Quantity	5
Outer Dimensions (inches)	9.7x6.2x3.5
Weight Uom	70 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website