



Representative

**Catalog Number:** H200CAPCP  
**Product ID:** 7TBD013430R0016  
**UPC Number:** 78621091169  
**Status:** A

2 Inch Zinc Capoff with Chrome Plating, Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- CSA Certified for hazardous locations Class II Groups E.F.G. Class III
- Meets NEMA sealing requirements for NEMA 3R, 4 & 13 enclosures.

### North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Hubs & Accessories
Special Features	Insulating Throat with a Thermoplastic Temperature Rating of 105 Degrees Celsius
Application	For Use with Rigid/IMC Conduit
Standard	UL E23018, CSA
Trade Size	2 in
Outside Diameter	3-1/4 in
Length	1-27/32 in
Material	Zinc with Chrome Plating

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

### Packaging

Outer Quantity	5
Outer Dimensions (inches)	3.75x3.5x6.75
Weight Uom	17 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website