



Representative

Catalog Number: H250BHD
Product ID: 7TBD013080R0023
UPC Number: 78621000292
Status: A

2-1/2 Inch Zinc Bulkhead Fittings with Thermoplastic Insulating Throat, Sealing Ring Nitrile (BUNA-N) for Use with Rigid/IMC Conduit

- For use with rigid/IMC conduit

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	Bulkhead Fitting
Special Features	Thermoplastic Insulating Throat with Rating up to 105 Degree Celsius
Application	A Fitting for Connecting a Junction Box to a Conduit System
Standard	UL E23018, CSA
Trade Size	2-1/2 in
Outside Diameter	3-3/4 in
Material	Zinc

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 1/2 inch
Model	Straight
Revolving thread	N
Connection type screw connection to housing	Thread
Thread type	NPT
Material housing	Zinc die-cast
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

Packaging

Outer Quantity	5
Outer Dimensions (inches)	10.7x8.3x4.5
Weight Uom	2.71 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------