



**Catalog Number:** HS4-30-M  
**Product ID:** 7TAA017010R0005  
**UPC Number:** 78621096142  
**Status:** A



Heat Shrink Tubing, Cable Range #4-3/0 AWG, 5 Inches, Black

Actual

**North American Specifications (UNSPSC)**

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heat Shrinkable Tubing
Shrink Ratio	3:1
Voltage Rating	600 V
Length	5 in ; 127 mm
Dielectric Strength	500 V/Mil (20kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +230 F ; -55 to +110 C
Minimum Shrink Temperature	248 F ; 120 C
Water Absorption	0.10%
Color	Black

**European Specifications (ETIM)**

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	3:1
Inner diameter before heat-shrink	27.94mm
Inner diameter after heat-shrink	8.89mm
Nominal diameter inch	Other
Wall thickness after shrinking	3.048mm
Length	0.127m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	N

**Packaging**

Inner Quantity	5
Inner Dimensions (inches)	6x2x9
Outer Quantity	50
Outer Dimensions (inches)	13x6x13
Weight Uom	3.13 lbs. per 100

**Documents / Support Tools**

Safety Data Sheet (SDS) Global	SDS-00046-TB2
--------------------------------	---------------