



Catalog Number: HS500-1000-4M
Product ID: 7TAA017010R0007
UPC Number: 78621096173
Status: A



Actual

Heat Shrink Tubing, Cable Range 500-1000MCM, 48 Inches, Black

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heat Shrinkable Tubing
Shrink Ratio	3:1
Voltage Rating	600 V
Length	48 in ; 304.8 mm
Dielectric Strength	500 V/Mil (20kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +230 F ; -55 to +110 C
Minimum Shrink Temperature	248 F ; 120 C
Water Absorption	0.10%
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	3:1
Inner diameter before heat-shrink	50.8mm
Inner diameter after heat-shrink	16.002mm
Nominal diameter inch	2 inch
Wall thickness after shrinking	3.556mm
Length	1.2192m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	N

Packaging

Inner Quantity	1
Outer Quantity	25
Outer Dimensions (inches)	6.75x51x19.25
Weight Uom	140 lbs. per 100

Documents / Support Tools

Safety Data Sheet (SDS) Global	SDS-00046-TB2
--------------------------------	---------------