



Actual

Catalog Number: HSMR12-6-4
Product ID: 7TAA017130R0000
UPC Number: 78621092837
Status: Active

Heavy-Wall Heat-Shrinkable Tubing - Flame Retardant for Cable Range 8 - 6 AWG, Expanded Diameter .51 inch, Length 48 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Insulates and protects electrical splices and terminations.
- High-impact and abrasion resistance.
- Thermoplastic adhesive lining.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Heavy-Wall Heat-Shrinkable Tubing
Special Features	Insulates and protects electrical splices and terminations.
Shrink Ratio	3:1
Voltage Rating	600V
Length	48 in
Flammability	UL 94 V-0
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	3:1
Inner diameter before heat-shrink	12.954mm
Inner diameter after heat-shrink	4.064mm
Nominal diameter inch	1/2 inch
Wall thickness after shrinking	22.86mm
Length	1.2m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

Packaging

Outer Quantity	25
Outer Dimensions (inches)	6x51x19
Weight Uom	21.88 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2

