



Actual

Catalog Number: HSHR2000-4
Product ID: 7TAA017120R0002
UPC Number: 78621024747
Status: Active

Heavy-Wall Heat-Shrinkable Tubing for Cable Range , Expanded Diameter 2, Length 48 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Accomodates a wide variety of connector shapes and configurations.
- Thermoplastic Adhesive Liner for complete environment protection and insulation.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Heavy-Wall Heat-Shrinkable Tubing
Special Features	Accomodates a wide variety of connector shapes and configurations.
Standard	UL E9809
Shrink Ratio	6:1
Voltage Rating	600V
Length	48 in
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	Other
Inner diameter before heat-shrink	50.8mm
Inner diameter after heat-shrink	8.382mm
Nominal diameter inch	2 inch
Wall thickness after shrinking	3.302mm
Length	1.2m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

Packaging

Outer Quantity	25
Outer Dimensions (inches)	6x49x19
Weight Uom	48 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2

