



Actual

Catalog Number: HSHR3500-4
Product ID: 7TAA017120R0004
UPC Number: 78621024749
Status: A

Heavy-Wall Heat-Shrinkable Tubing for Cable Range , Expanded Diameter 3.5 inch, Length 48 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Accomodates a wide variety of connector shapes and configurations.
- Thermoplastic Adhesive Liner for complete environment protection and insulation.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Heavy-Wall Heat Shrinkable Tubing
Special Features	Accomodates a wide variety of connector shapes and configurations.
Shrink Ratio	6:1
Voltage Rating	600 V
Length	48 in
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thick-walled
Shrink rate	Other
Inner diameter before heat-shrink	88.9mm
Inner diameter after heat-shrink	14.732mm
Nominal diameter inch	Other
Wall thickness after shrinking	3.81mm
Length	1.22m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

Packaging

Outer Quantity	10
Outer Dimensions (inches)	6x49x19
Weight Uom	9 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2