

Catalog Number: HSHR750-4
Product ID: 7TAA017120R0006
UPC Number: 78621024744
Status: A



Heavy-Wall Heat-Shrinkable Tubing for Cable Range , Expanded Diameter 3/4 inch, Length 48 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Accomodates a wide variety of connector shapes and configurations.
- Thermoplastic Adhesive Liner for complete environment protection and insulation.

Actual

North American Specifications (UNSPSC)

| | |
|------------------|---|
| UNSPSC | 39121723 Heat shrinkable tube |
| IGCC | 5073 Heat shrinkable tube |
| Type | Heavy-Wall Heat Shrinkable Tubing |
| Special Features | Accommodates a wide variety of connector shapes and configurations. |
| Shrink Ratio | 6:1 |
| Voltage Rating | 600 V |
| Length | 48 in |
| Color | Black |

European Specifications (ETIM)

| | |
|-----------------------------------|------------------------|
| ETIM | EC000217 Shrink tubing |
| Type | Heat-shrink |
| Model | Thick-walled |
| Shrink rate | Other |
| Inner diameter before heat-shrink | 19.05mm |
| Inner diameter after heat-shrink | 3.302mm |
| Nominal diameter inch | 3/4 inch |
| Wall thickness after shrinking | 2.54mm |
| Length | 1.22m |
| Operation temperature | -55-+110°C |
| Colour | Black |
| Material | Polyolefin (PO-X) |
| Halogen free | N |
| With inner glue | Y |
| Printable | N |
| UL approval | N |

Packaging

| | |
|---------------------------|-----------------|
| Outer Quantity | 25 |
| Outer Dimensions (inches) | 4x49x4 |
| Weight Uom | 12 lbs. per 100 |

Documents / Support Tools

| | |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
| Catalog Page | Available on Website |
| Safety Data Sheet (SDS) Global | SDS-00046-TB2 |