



Catalog Number: **ISR100-102SS**
Product ID: 7TBA297200R0004
UPC Number: 78621020709
EAN Number: 05011949245815
Status: A

Industrial Strain-Relief Fitting, Hub Size 1 Inch NPT, Cable Range 19.94 to 26.04mm, CSA and UL Listed, Outer Diameter 48.26mm, Stainless Steel

North American Specifications (UNSPSC)

UNSPSC	39121719 Strain reliefs
IGCC	5067 Strain reliefs
Type	Industrial Strain Relief Fitting
Special Features	100% of IEC Cable Pull-Out Requirements with No External Clamping
Application	Connection and Strain Relief for Conduit Systems
Standard	CSA, UL E328651 and E311979
Cable Size	19.94 to 26.04 mm
Hub Size	1 in
Material	Stainless Steel
Color	Metallic

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Stainless steel
Operating temperature	-50-+110°C

Packaging

Outer Quantity	10
Outer Dimensions (inches)	5.94x5.94x4.69
Weight Uom	68.15 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001684
Support/Tools	Available on Website