

Catalog Number: **ISR150-156SS**
Product ID: 7TBA297200R0007
UPC Number: 78621020711
EAN Number: 05011949245839
Status: A

Industrial Strain-Relief Fitting, Hub Size 1-1/2 Inch NPT, Cable Range 33.91 to 39.37mm, CSA and UL Listed, Outer Diameter 65.53mm, Stainless Steel

North American Specifications (UNSPSC)

UNSPSC	39121719 Strain reliefs
IGCC	5067 Strain reliefs
Brand Name	ABB
Type	Industrial Strain Relief Fitting
Special Features	100% of IEC Cable Pull-Out Requirements with No External Clamping
Application	Connection and Strain Relief for Conduit Systems
Standard	CSA, UL E328651 and E311979
Cable Size	33.91 to 39.37 mm
Hub Size	1-1/2 in
Material	Stainless Steel
Color	Metallic

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Stainless steel
Operating temperature	-50-+110°C

Packaging

Outer Quantity	5
Outer Dimensions (inches)	9x4.69x4.13
Weight Uom	123.25 lbs. per 100