



Actual

Catalog Number: **ISR200-179**
Product ID: 7TBA297190R0007
UPC Number: 78621005950
EAN Number: 05011949235830
Status: A

Industrial Strain-Relief Fitting, Hub Size 2 Inch NPT, Cable Range 38.73 to 45.34mm, CSA and UL Listed, Outer Diameter 76.50mm, Aluminum

- For use with unarmoured cable types suitable for use in Class I, Zone 1
- Tray Cable complies with IEC requirements when used with enclosures containing no arcing or sparking devices.
- Portable Cord complies with IEC requirements when used with enclosures containing no arcing or sparking devices

North American Specifications (UNSPSC)

UNSPSC	39121719 Strain reliefs
IGCC	5067 Strain reliefs
Type	Industrial Strain Relief Fitting
Special Features	100% of IEC Cable Pull-Out Requirements with No External Clamping
Application	Connection and Strain Relief for Conduit Systems
Standard	CSA, UL E328651 and E311979
Cable Size	38.73 to 45.34 mm
Hub Size	2 in
Material	Aluminum
Color	Metallic

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Operating temperature	-50-+110°C

Packaging

Outer Quantity	5
Outer Dimensions (inches)	9.07x6.57x5.13
Weight Uom	71.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001684
Catalog Page	Available on Website
Support/Tools	Available on Website