

**Catalog Number:** **ISR200-206SS**  
**Product ID:** 7TBA297200R0009  
**UPC Number:** 78621020713  
**EAN Number:** 05011949245853  
**Status:** A

Industrial Strain-Relief Fitting, Hub Size 2 Inch NPT, Cable Range 44.58 to 52.20mm, CSA and UL Listed, Outer Diameter 81.28mm, Stainless Steel

#### North American Specifications (UNSPSC)

UNSPSC	39121719 Strain reliefs
IGCC	5067 Strain reliefs
Brand Name	ABB
Type	Industrial Strain Relief Fitting
Special Features	100% of IEC Cable Pull-Out Requirements with No External Clamping
Application	Connection and Strain Relief for Conduit Systems
Standard	CSA, UL E328651 and E311979
Cable Size	44.58 to 52.2 mm
Hub Size	2 in
Material	Stainless Steel
Color	Metallic

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Stainless steel
Operating temperature	-50-+110°C

#### Packaging

Outer Quantity	5
Outer Dimensions (inches)	9.07x6.57x5.13
Weight Uom	181.25 lbs. per 100