



Actual

Catalog Number: LB50MCG
Product ID: 7TAD013210R0050
UPC Number: 78620986857
Status: A

1/2 Inch Series 35 Unipak Type LB Conduit Body, Cover and Gasket, Body Material and Finish Malleable Iron Zinc Plated with Aluminum, Acrylic Coating, Cover Material and Finish Stamped Steel Zinc Plated, Gasket Material Neoprene

- All threaded hubs have tapered threads.
- Suitable for use in concrete
- Serve as pulling outlets during conductor installation
- Provide easy access for splices in branch conductors
- Make 90 degree bends in conduit runs
- Act as mounting outlets for wiring devices and lighting fixtures
- Provide access to conductors for maintenance and future system changes

North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Type	Series 35 Unipak Conduit Body, Cover & Gasket
Special Features	Zinc-Plated Iron Construction with Aluminum Acrylic Coating Provides Durability, Impact Resistance and Corrosion Resistance.
Application	To Connect Conduit Sections
Standard	UL E2969
Hub Size	1/2 in
Material	Malleable Iron
Finish	Zinc Plating with Aluminum Acrylic Coating

Packaging

Outer Quantity	10
Outer Dimensions (inches)	8x5x4.75
Weight Uom	98.25 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000301
Catalog Page	Available on Website