



Representative

Catalog Number: LR125M
Product ID: 7TAD013210R0066
UPC Number: 78621096168
Status: A

Series 35 Right Side Opening 1-1/4 Inch Conduit Body, Body Material Malleable Iron, Finish Zinc Plating with an Aluminum, Acrylic Coating for Use with Rigid/IMC Conduit

- Features tapered, threaded NPT hubs.
- Covers available in iron or stamped steel, both zinc-plated and supplied with stainless steel captive screws.
- Suitable for use in concrete.
- Serve as pulling outlets during conductor installation
- Provide easy access for splices in branch conductors
- Make 90 degree bends in conduit runs
- Act as mounting outlets for wiring devices and lighting fixtures
- Provide access to conductors for maintenance and future system changes

North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Brand Name	T&B
Type	Series 35 Conduit Body
Special Features	Zinc-Plated Iron Construction with Aluminum Acrylic Coating Provides Durability, Impact Resistance and Corrosion Resistance.
Application	To Connect Conduit Sections
Standard	UL E2969, CSA
Hub Size	1-1/4 in
Material	Malleable Iron
Finish	Zinc Plating with Aluminum Acrylic Coating

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	5
Outer Dimensions (inches)	14x8.5x4
Weight Uom	3.32 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000256
Technical Drawing / Data Sheet Canada	Available on Website