



Representative

**Catalog Number:** LR200M  
**Product ID:** 7TAD013210R0068  
**UPC Number:** 78621096179  
**Status:** A

Series 35 Right Side Opening 2 Inch Conduit Body, Body Material Malleable Iron, Finish Zinc Plating with an Aluminum, Acrylic Coating for Use with Rigid/IMC Conduit

- Features tapered, threaded NPT hubs.
- Covers available in iron or stamped steel, both zinc-plated and supplied with stainless steel captive screws.
- Suitable for use in concrete.
- Serve as pulling outlets during conductor installation
- Provide easy access for splices in branch conductors
- Make 90 degree bends in conduit runs
- Act as mounting outlets for wiring devices and lighting fixtures
- Provide access to conductors for maintenance and future system changes

**North American Specifications (UNSPSC)**

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Type	Series 35 Conduit Body
Special Features	Zinc-Plated Iron Construction with Aluminum Acrylic Coating Provides Durability, Impact Resistance and Corrosion Resistance.
Application	To Connect Conduit Sections
Standard	UL E2969, CSA
Hub Size	2 in
Material	Malleable Iron
Finish	Zinc Plating with Aluminum Acrylic Coating

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	10.75x8.75x4.87
Weight Uom	6.26 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-000256
--------------------------------	------------