



Catalog Number: LR67SA
Product ID: 7TAA0130A0R0051
UPC Number: 78621010391
Status: A



Actual

2 Inch Conduit Body, LR Shape, Form 7, For Use with Rigid/IMC Conduit, UL Standard, CSA Compliant, Fed Spec W-C-586D, Sand-Cast Aluminum Alloy

- Standard features include tapered (NPT) threads and integral bushings to protect wire insulation
- Conduit bodies and covers are interchangeable with Crouse Hinds, Appleton and OZ Gedney form 7 conduit bodies
- Ideal for use in food and beverage, pharmaceutical, chemical processing and other corrosive environments
- Act as pull outlets when conductors are being installed
- Provide easy access for splices in branch conductors
- Make 90 degree bends in conduit runs
- Act as mounting outlets for wiring devices and lighting fixtures
- Provide access to conductors for maintenance and future system changes

North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Type	Conduit Body - Type LR
Special Features	Special aluminum alloy provides superior corrosion resistance as cast. No protective coatings needed
Application	Ideal for use in food and beverage, pharmaceutical, chemical processing and other corrosive environments
Standard	UL Standard, CSA Complaint, Fed Spec W-C-586D
Form	Form 7
Material	Sand Cast Aluminum

Packaging

Inner Quantity	2
Inner Dimensions (inches)	9.5x4.5x6.5
Outer Quantity	10
Outer Dimensions (inches)	12.5x9.75x8
Weight Uom	1.77 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	WSD-001034
Marketing Brochure US	Available on Website