



**Catalog Number:** LS-7.9-1010B  
**Product ID:** 7TAG009420R0016  
**UPC Number:** 78621024237  
**EAN Number:** 05414363126195  
**Status:** A



Ball-Lock 316 Stainless Steel Cable Tie, Uncoated, for Temperatures up to 300 Degrees Celsius (572 F) for Indoor and Outdoor Applications, Suitable for High Temperature Environments, UL/EN/CSA62275 Type 2S Rated for AH-1 Plenum, Length of 1010mm (39.8 Inches), Width of 7.75mm (0.305 inches), Thickness of 0.25mm (0.01 Inches), Tensile Strength Rating of 2002 Newtons (450 Pounds)

- Application Tools: DAS-250

Actual

**North American Specifications (UNSPSC)**

UNSPSC	39121703 Cable ties
IGCC	5046 Stainless Steel Ties
Type	Stainless Steel
Standard	UL E49405
Width	0.305 in ; 7.75 mm
Length	39.8 in ; 1010 mm
Bundle Diameter	0.38 to 12 in ; 9.7 to 304 mm
Material	316 Stainless Steel
Color	Metallic Gray
Lock Mechanism	Ball-Lock
Tensile Strength	450 pounds ; 2002 newtons

**European Specifications (ETIM)**

ETIM	EC000046 Cable tie
Band width	7.75mm
Length belt/tape/tie	1010mm
Tie thickness	0.25mm
Min. holding force	2002N
Band closure	Ball latch
Material	Metal
Material quality	Stainless steel 316 (V4A)
Halogen free	Y
Colour	Stainless steel
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

**Packaging**

Inner Quantity	50
Outer Quantity	1000
Weight Uom	5.38 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-001005
--------------------------------	------------

