



Representative

Catalog Number: LT200P
Product ID: 7TAD012550R0004
UPC Number: 78621045070
EAN Number: 05414363100577
Status: A

2 Inch Non-Metallic Liquidtight Bullet Connector

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.
- Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Bullet-Straight
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	2 Inch
Material	Thermoplastic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	20.17mm
Material screw gland	Other
Material sealing	Other
Colour	Black

Packaging

Outer Quantity	5
Outer Dimensions (inches)	21.7x6.4x5.3
Weight Uom	56.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000236
Instruction Sheet	TA00998-TB2

Header

3D Model	Available on Website
----------	----------------------

