



Representative

**Catalog Number:** LT4100P-200  
**Product ID:** 7TAD012550R0007  
**UPC Number:** 78621090862  
**Status:** A

1/2 Inch 90 Degree Bullet Non-metallic Conduit Fitting for Liquidtight FNMC Type B. 200 Pieces, Weather Stabilized Thermoplastic Material UL Listed for Direct Burial. IP66 and IP68 At 2 Meters. Use Only With TB Conduit LTC050 Or LTC050 to 1. 200 Pieces

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Liquidtight Fittings
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	1 Inch
Material	Non-Metallic

### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	18.44mm
Material screw gland	Other
Material sealing	Other
Colour	Black

### Packaging

Outer Quantity	200
Outer Dimensions (inches)	19x14x13
Weight Uom	25.8 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000236
Catalog Page	Available on Website