



Representative

**Catalog Number:** LT4150P  
**Product ID:** 7TAD012570R0001  
**UPC Number:** 78621045086  
**EAN Number:** 05414363100621  
**Status:** A

1-1/2 Inch 45 Degree Non-Metallic Liquidtight Bullet Connector

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.
- Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Bullet-45 Degree
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	1-1/2 Inch
Material	Thermoplastic

#### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1 1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	19.48mm
Material screw gland	Other
Material sealing	Other
Colour	Black

#### Packaging

Inner Quantity	2
Inner Dimensions (inches)	6x5x4
Outer Quantity	10
Outer Dimensions (inches)	26.7x6.8x5.1
Weight Uom	55 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000236
Instruction Sheet	TA00998-TB2

#### Header

3D Model	Available on Website
----------	----------------------

