



Representative

Catalog Number: LT438M
Product ID: 7TAD012600R0006
UPC Number: 78621045043
EAN Number: 05414363182924
Status: A

3/8 Inch 45 Degree Steel Liquidtight Bullet With Nylon Insert

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Bullet-45 Degree
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	3/8 Inch
Material	Steel

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/8 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	14.3mm
Material screw gland	Metal
Material sealing	Polyamide
Colour	Other

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4x4
Outer Quantity	50
Outer Dimensions (inches)	9.1x5.3x7
Weight Uom	14.56 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00972-TB2

Header

3D Model	Available on Website
----------	----------------------