



Representative

**Catalog Number:** LT450M  
**Product ID:** 7TAD012590R0003  
**UPC Number:** 78621045044  
**EAN Number:** 05414363154846  
**Status:** A

1/2 Inch 45 Degree Steel Liquidtight Bullet With Nylon Insert

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Bullet-45 Degree
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Steel

### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	14.3mm
Material screw gland	Metal
Material sealing	Polyamide
Colour	Other

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	8.7x5.6x8.8
Weight Uom	31 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA00972-TB2

### Header

3D Model	Available on Website
----------	----------------------