



Representative

Catalog Number: LT450P-500
Product ID: 7TAD012550R0010
UPC Number: 78621089486
EAN Number: 05414363154853
Status: A

1/2 Inch 45 Degree Straight Non-metallic Conduit Fitting for Liquidtight FNMC Type B, Meets Nema Ratings: 4, 4X, 6, 6P, 12 and 13, Weather Stabilized Thermoplastic Material

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B Industrial Fitting
Type	Liquidtight Flexible Nonmetallic Conduit Fittings
Application	For NMC & NMT
Standard	CSA, UL
Size	1/2 Inch
Material	Thermoplastic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	14.48mm
Material screw gland	Other
Material sealing	Other
Colour	Black

Packaging

Outer Quantity	500
Outer Dimensions (inches)	19x14x13
Weight Uom	7.06 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000236
Technical Drawing / Data Sheet Canada	Available on Website