




**Catalog Number:** LT4GES01C-L  
**Product ID:** 7TAA012LU0R0017  
**UPC Number:** 78621015430  
**EAN Number:** 05415022446418  
**Status:** A



Liquid Tight Flexible Metallic Conduit, 304 Stainless Steel Core with PVC Jacket, Conduit Size 3/8 Inch, Length 300 Meters/1,000 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, Clear

Representative

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	3/8 in
Outside Diameter	0.71 in
Inside Diameter	0.484 in
Length	1,000 ft
Material	304 Stainless Steel Core with PVC Jacket
Color	Clear

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	16mm
Nominal size in inch	3/8 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Other
Bending strength	Flexible

#### Packaging

Outer Quantity	1000
Outer Dimensions (inches)	20x30x30
Weight Uom	0.22 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000085
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website