




Catalog Number: LT4GES04C-C
Product ID: 7TAA012LU0R0003
UPC Number: 78621015415
EAN Number: 05415022446272
Status: A



Liquid Tight Flexible Metallic Conduit, 304 Stainless Steel Core with PVC Jacket, Conduit Size 1 Inch, Length 30 Meters/100 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, Clear

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1 in
Outside Diameter	1.315 in
Inside Diameter	1.041 in
Length	100 ft
Material	304 Stainless Steel Core with PVC Jacket
Color	Clear

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	32mm
Nominal size in inch	1 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Other
Bending strength	Flexible

Packaging

Outer Quantity	100
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	0.53 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000085
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website