



**Catalog Number:** LT4GES06C-B  
**Product ID:** 7TAA012LU0R0005  
**UPC Number:** 78621015417  
**EAN Number:** 05415022446296  
**Status:** A



Liquid Tight Flexible Metallic Conduit, 304 Stainless Steel Core with PVC Jacket, Conduit Size 1-1/2 Inch, Length 15 Meters/50 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, Clear

Representative

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1-1/2 in
Outside Diameter	1.9 in
Inside Diameter	1.575 in
Length	50 ft
Material	304 Stainless Steel Core with PVC Jacket
Color	Clear

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Other
Bending strength	Flexible

#### Packaging

Outer Quantity	50
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	0.88 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000085
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website