



Catalog Number: LT4GES08C-A
Product ID: 7TAA012LU0R0007
UPC Number: 78621015419
EAN Number: 05415022446319
Status: A



Liquid Tight Flexible Metallic Conduit, 304 Stainless Steel Core with PVC Jacket, Conduit Size 2-1/2 Inch, Length 8 Meters/25 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, Clear

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	2-1/2 in
Outside Diameter	2.875 in
Inside Diameter	2.48 in
Length	25 ft
Material	304 Stainless Steel Core with PVC Jacket
Color	Clear

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	70mm
Nominal size in inch	2 1/2 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Other
Bending strength	Flexible

Packaging

Outer Quantity	25
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	2.09 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000085
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website