



Representative

Catalog Number: LT50PISO20
Product ID: 7TAD012580R0002
UPC Number: 78621066443
EAN Number: 05414363100683
Status: A

1/2 Inch, Straight Non-Metallic ISO Metric Bullet Liquidtight Fitting

- T&B Bullet liquidtight fitting and LTC non-metallic conduit are suitable for construction applications where ISO metric threading and liquidtight systems are installed.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	ISO Metric Bullet-Straight
Application	T&B Bullet liquidtight fitting and EFC non-metallic conduit are suited for OEM applications as in the machine tool industry where environments include continuous motion, vibration and exposure to moisture, oil, dirt and dust.
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Thermoplastic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	M20 x 1.5
Thread length	14.48mm
Material screw gland	Other
Material sealing	Other
Colour	Black

Packaging

Inner Quantity	20
Inner Dimensions (inches)	6x5x4
Outer Quantity	100
Outer Dimensions (inches)	26.2x9x5
Weight Uom	6 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000236
Instruction Sheet	TA00998-TB2

Header

3D Model	Available on Website
----------	----------------------