

**Catalog Number:** LT6FES01W-C  
**Product ID:** 7TAA012LX0R0000  
**UPC Number:** 78621015459  
**EAN Number:** 05415022446845  
**Status:** Active



Liquid Tight Flexible Metallic Conduit, Food and Beverage Grade, 316 Stainless Steel Core with PVC Jacket, Conduit Size 3/8 Inch, Length 30 Meters/100 Feet, Working Temperature -45 to 105 Degrees C, Compliant to RoHS and WEEE, White

Representative

### North American Specifications (UNSPSC)

|                  |  |
|------------------|--|
| UNSPSC           | 39131706 Electrical conduit              |
| IGCC             | 5543 Liquid Tight Conduit                |
| Brand Name       | T&B                                      |
| Type             | Flexible Metal Conduit                   |
| Standard         | RoHS, WEEE                               |
| Trade Size       | 3/8 Inch                                 |
| Outside Diameter | 0.71                                     |
| Inside Diameter  | 0.484                                    |
| Length           | 100 ft                                   |
| Material         | 316 Stainless Steel Core with PVC Jacket |
| Color            | White                                    |

### European Specifications (ETIM)

|   |                                   |
|---|-----------------------------------|
| ETIM                                      | EC001179 Protective metallic hose |
| Nominal diameter                          | 16mm                              |
| Nominal size in inch                      | 3/8 inch                          |
| Material                                  | Stainless steel                   |
| Sheathing material 2nd coating (exterior) | PVC                               |
| Operating temperature                     | -45-+105°C                        |
| Colour                                    | White                             |
| Bending strength                          | Flexible                          |

### Packaging

|                           |                |
|---------------------------|----------------|
| Outer Quantity            | 100            |
| Outer Dimensions (inches) | 17.62x16.75x8  |
| Weight Uom                | 0.21 lbs. Each |

### Documents / Support Tools

|                                       |                      |
|---------------------------------------|----------------------|
| Technical Drawing / Data Sheet        | TDS000086            |
| Technical Drawing / Data Sheet        | TDS000117            |
| Technical Drawing / Data Sheet Canada | TDS000086            |
| Catalog US                            | Available on Website |