




**Catalog Number:** LT6FES02W-L  
**Product ID:** 7TAA012LX0R0018  
**UPC Number:** 78621015477  
**EAN Number:** 05415022447026  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Food and Beverage Grade, 316 Stainless Steel Core with PVC Jacket, Conduit Size 1/2 Inch, Length 300 Meters/1,000 Feet, Working Temperature -45 to 105 Degrees C, Compliant to RoHS and WEEE, White

Representative

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1/2 in
Outside Diameter	0.84 in
Inside Diameter	0.622 in
Length	1,000 ft
Material	316 Stainless Steel Core with PVC Jacket
Color	White

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-45-+105°C
Colour	White
Bending strength	Flexible

**Packaging**

Outer Quantity	1000
Outer Dimensions (inches)	20x30x30
Weight Uom	0.25 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000086
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website