




**Catalog Number:** LT6FES05W-B  
**Product ID:** 7TAA012LX0R0004  
**UPC Number:** 78621015463  
**EAN Number:** 05415022446883  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Food and Beverage Grade, 316 Stainless Steel Core with PVC Jacket, Conduit Size 1-1/4 Inch, Length 15 Meters/50 Feet, Working Temperature -45 to 105 Degrees C, Compliant to RoHS and WEEE, White

Representative

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1-1/4 in
Outside Diameter	1.66 in
Inside Diameter	1.38 in
Length	50 ft
Material	316 Stainless Steel Core with PVC Jacket
Color	White

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-45-+105°C
Colour	White
Bending strength	Flexible

#### Packaging

Outer Quantity	50
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	0.61 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000086
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website