

Catalog Number: LT6FES06W-D
Product ID: 7TAA012LX0R0015
UPC Number: 78621015474
EAN Number: 05415022446999
Status: Active



Liquid Tight Flexible Metallic Conduit, Food and Beverage Grade, 316 Stainless Steel Core with PVC Jacket, Conduit Size 1-1/2 Inch, Length 45 Meters/150 Feet, Working Temperature -45 to 105 Degrees C, Compliant to RoHS and WEEE, White

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1-1/2 Inch
Outside Diameter	1.9
Inside Diameter	1.575
Length	150 ft
Material	316 Stainless Steel Core with PVC Jacket
Color	White

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-45-+105°C
Colour	White
Bending strength	Flexible

Packaging

Outer Quantity	150
Outer Dimensions (inches)	20x32x32
Weight Uom	0.78 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000086
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000086
Catalog US	Available on Website