


Catalog Number: LT6GES01G-K
Product ID: 7TAA012LV0R0010
UPC Number: 78621015445
EAN Number: 05415022446548
Status: Active



Liquid Tight Flexible Metallic Conduit, 316 Stainless Steel Core with PVC Jacket, Conduit Size 3/8 Inch, Length 150 Meters/500 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, Gray

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	3/8 Inch
Outside Diameter	0.71
Inside Diameter	0.484
Length	500 ft
Material	316 Stainless Steel Core with PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	16mm
Nominal size in inch	3/8 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	500
Outer Dimensions (inches)	20x24x24
Weight Uom	0.21 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000087
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000087
Catalog US	Available on Website