


Catalog Number: LT6GES05G-B
Product ID: 7TAA012LV0R0004
UPC Number: 78621015439
EAN Number: 05415022446487
Status: Active



Liquid Tight Flexible Metallic Conduit, 316 Stainless Steel Core with PVC Jacket, Conduit Size 1-1/4 Inch, Length 15 Meters/50 Feet, Working Temperature -20 to 80 Degrees C, Compliant to RoHS and WEEE, Gray

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1-1/4 Inch
Outside Diameter	1.66
Inside Diameter	1.38
Length	50 ft
Material	316 Stainless Steel Core with PVC Jacket
Color	Gray

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	PVC
Operating temperature	-20-+80°C
Colour	Grey
Bending strength	Flexible

Packaging

Outer Quantity	50
Outer Dimensions (inches)	25.25x24.5x8.25
Weight Uom	0.7 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000087
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000087
Catalog US	Available on Website