



Catalog Number: LT6XES02B-L
Product ID: 7TAA012LW0R0018
UPC Number: 78621015497
EAN Number: 05415022446821
Status: A



Liquid Tight Flexible Metallic Conduit, Extreme Temperature, 316 Stainless Steel Core with TRP Jacket (UL94-HB), Conduit Size 1/2 Inch, Length 300 Meters/1,00 Feet, Working Temperature -55 to 150 Degrees C, Compliant to RoHS and WEEE, Black

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1/2 in
Outside Diameter	0.84 in
Inside Diameter	0.622 in
Length	1,000 ft
Material	316 Stainless Steel Core with TRP Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	Other
Operating temperature	-55-+150°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	1000
Outer Dimensions (inches)	20x30x30
Weight Uom	0.24 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000088
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website