

**Catalog Number:** LT6XES03B-C  
**Product ID:** 7TAA012LW0R0002  
**UPC Number:** 78621015481  
**EAN Number:** 05415022446661  
**Status:** Active



Liquid Tight Flexible Metallic Conduit, Extreme Temperature, 316 Stainless Steel Core with TRP Jacket (UL94-HB), Conduit Size 3/4 Inch, Length 30 Meters/100 Feet, Working Temperature -55 to 150 Degrees C, Compliant to RoHS and WEEE, Black

Actual

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	3/4 Inch
Outside Diameter	1.05
Inside Diameter	0.82
Length	100 ft
Material	316 Stainless Steel Core with TRP Jacket
Color	Black

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	Other
Operating temperature	-55-+150°C
Colour	Black
Bending strength	Flexible

### Packaging

Outer Quantity	100
Outer Dimensions (inches)	20.75x20.38x8
Weight Uom	0.29 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000088
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000088
Catalog US	Available on Website