

Catalog Number: LT6XES06B-B
Product ID: 7TAA012LW0R0005
UPC Number: 78621015484
EAN Number: 05415022446692
Status: Active



Liquid Tight Flexible Metallic Conduit, Extreme Temperature, 316 Stainless Steel Core with TRP Jacket (UL94-HB), Conduit Size 1-1/2 Inch, Length 15 Meters/50 Feet, Working Temperature -55 to 150 Degrees C, Compliant to RoHS and WEEE, Black

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1-1/2 Inch
Outside Diameter	1.9
Inside Diameter	1.575
Length	50 ft
Material	316 Stainless Steel Core with TRP Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	Other
Operating temperature	-55-+150°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	50
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	0.88 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000088
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000088
Catalog US	Available on Website