



**Catalog Number:** LT6XES06B-D  
**Product ID:** 7TAA012LW0R0015  
**UPC Number:** 78621015494  
**EAN Number:** 05415022446791  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Extreme Temperature, 316 Stainless Steel Core with TRP Jacket (UL94-HB), Conduit Size 1-1/2 Inch, Length 45 Meters/150 Feet, Working Temperature -55 to 150 Degrees C, Compliant to RoHS and WEEE, Black

Representative

**North American Specifications (UNSPSC)**

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	1-1/2 in
Outside Diameter	1.9 in
Inside Diameter	1.575 in
Length	150 ft
Material	316 Stainless Steel Core with TRP Jacket
Color	Black

**European Specifications (ETIM)**

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	Other
Operating temperature	-55-+150°C
Colour	Black
Bending strength	Flexible

**Packaging**

Outer Quantity	150
Outer Dimensions (inches)	20x32x32
Weight Uom	0.88 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000088
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website