



**Catalog Number:** LT6XES09B-A  
**Product ID:** 7TAA012LW0R0008  
**UPC Number:** 78621015487  
**EAN Number:** 05415022446722  
**Status:** A



Liquid Tight Flexible Metallic Conduit, Extreme Temperature, 316 Stainless Steel Core with TRP Jacket (UL94-HB), Conduit Size 3 Inch, Length 8 Meters/25 Feet, Working Temperature -55 to 150 Degrees C, Compliant to RoHS and WEEE, Black

Representative

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	3 in
Outside Diameter	3.5 in
Inside Diameter	3.07 in
Length	25 ft
Material	316 Stainless Steel Core with TRP Jacket
Color	Black

#### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	80mm
Nominal size in inch	3 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	Other
Operating temperature	-55-+150°C
Colour	Black
Bending strength	Flexible

#### Packaging

Outer Quantity	25
Outer Dimensions (inches)	8.5x50x50
Weight Uom	2.87 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000088
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website