


Catalog Number: LT6XES11B-A
Product ID: 7TAA012LW0R0009
UPC Number: 78621015488
EAN Number: 05415022446739
Status: Active



Liquid Tight Flexible Metallic Conduit, Extreme Temperature, 316 Stainless Steel Core with TRP Jacket (UL94-HB), Conduit Size 4 Inch, Length 8 Meters/25 Feet, Working Temperature -55 to 150 Degrees C, Compliant to RoHS and WEEE, Black

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	T&B
Type	Flexible Metal Conduit
Standard	RoHS, WEEE
Trade Size	4 Inch
Outside Diameter	4.5
Inside Diameter	4
Length	25 ft
Material	316 Stainless Steel Core with TRP Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	100mm
Nominal size in inch	4 inch
Material	Stainless steel
Sheathing material 2nd coating (exterior)	Other
Operating temperature	-55-+150°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	25
Outer Dimensions (inches)	6.5x60.25x60.25
Weight Uom	3.78 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000088
Technical Drawing / Data Sheet	TDS000117
Technical Drawing / Data Sheet Canada	TDS000088
Catalog US	Available on Website