



Representative

Catalog Number: LT9150M
Product ID: 7TAD012600R0009
UPC Number: 78621045055
EAN Number: 05414363182931
Status: A

1-1/2 Inch 90 Degree Steel Liquidtight Bullet With Nylon Insert

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Bullet-90 Degree
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	1-1/2 Inch
Material	Steel

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1 1/2 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	20.6mm
Material screw gland	Metal
Material sealing	Polyamide
Colour	Other

Packaging

Inner Quantity	2
Inner Dimensions (inches)	6x5x4
Outer Quantity	10
Outer Dimensions (inches)	20.9x5.7x9.1
Weight Uom	149 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00972-TB2

Header

3D Model	Available on Website
----------	----------------------