



Representative

**Catalog Number:** LT938M  
**Product ID:** 7TAD012600R0010  
**UPC Number:** 78621045050  
**EAN Number:** 05414363154983  
**Status:** A

3/8 Inch 90 Degree Steel Liquidtight Bullet With Nylon Insert

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Bullet-90 Degree
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	3/8 Inch
Material	Steel

#### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/8 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	15.9mm
Material screw gland	Metal
Material sealing	Polyamide
Colour	Other

#### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	50
Outer Dimensions (inches)	9.1x5.2x7
Weight Uom	19.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00972-TB2

#### Header

3D Model	Available on Website
----------	----------------------