



Representative

**Catalog Number:** LT938PISO20  
**Product ID:** 7TAD012580R0004  
**UPC Number:** 78621066613  
**EAN Number:** 05414363100768  
**Status:** Active

3/8 Inch, 90 Degree Non-Metallic ISO Metric Bullet Liquidtight Fitting

- T&B Bullet liquidtight fitting and LTC non-metallic conduit are suitable for construction applications where ISO metric threading and liquidtight systems are installed.

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	ISO Metric Bullet-90 Degree
Application	T&B Bullet Liquidtight Fitting and EFC Non-Metallic Conduit are Suited for OEM Applications As In the Machine Tool Industry Where Environments Include Continuous Motion, Vibration and Exposure to Moisture, Oil, Dirt and Dust.
Standard	UL E23018, CSA
Size	3/8 Inch
Material	Thermoplastic

### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/8 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	M20 x 1.5
Thread length	14.48mm
Material screw gland	Other
Material sealing	Other
Colour	Black

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x5x4
Outer Quantity	50
Outer Dimensions (inches)	26.4x6.25x4.5
Weight Uom	8.75 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

### Header

3D Model	Available on Website
----------	----------------------

