



Representative

Catalog Number: LT975PISO25
Product ID: 7TAD012580R0006
UPC Number: 78621066611
EAN Number: 05414363100805
Status: A

3/4 Inch, 90 Degree Non-Metallic ISO Metric Bullet Liquidtight Fitting

- T&B Bullet liquidtight fitting and LTC non-metallic conduit are suitable for construction applications where ISO metric threading and liquidtight systems are installed.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	ISO Metric Bullet-90 Degree
Application	T&B Bullet Liquidtight Fitting and EFC Non-Metallic Conduit are Suited for OEM Applications As In the Machine Tool Industry Where Environments Include Continuous Motion, Vibration and Exposure to Moisture, Oil, Dirt and Dust.
Standard	UL E23018
Size	3/4 Inch
Material	Thermoplastic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	M25 x 1.5
Thread length	14.78mm
Material screw gland	Other
Material sealing	Other
Colour	Black

Packaging

Inner Quantity	10
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	26.7x8.38x4.5
Weight Uom	14.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000236
Instruction Sheet	TA00998-TB2

Header

3D Model	Available on Website
----------	----------------------