



Catalog Number: LTBUS02L-L
Product ID: 7TAA012LFOR0021
UPC Number: 78621011200
EAN Number: 05415022393262
Status: A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1/2 Inch, Length 300 Meters/1,000 Feet, For Computer Data Systems, UL 360, CSA, Compliant to RoHS, Working Temperature -20 to 60 Degrees C, Blue

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	1/2 in ; 20 mm
Outside Diameter	0.840 in
Inside Diameter	0.622 in
Length	1,000 ft ; 300 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Blue

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Outer diameter	21.34mm
Inner diameter	15.80mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-20-+60°C
Colour	Blue
Bending strength	Flexible

Packaging

Outer Quantity	1000
Outer Dimensions (inches)	20x30x30
Weight Uom	0.33 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000009
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website