



Catalog Number: LTBUS03E-C
Product ID: 7TAA012LFOR0042
UPC Number: 78621011279
EAN Number: 05415022393477
Status: A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 3/4 Inch, Length 30 Meters/100 Feet, Special Purpose Use, UL 360, CSA, Compliant to RoHS, Working Temperature -20 to 60 Degrees C, Orange

Actual

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	3/4 in ; 25 mm
Outside Diameter	1.050 in
Inside Diameter	0.820 in
Length	100 ft ; 30 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Orange

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Outer diameter	26.67mm
Inner diameter	20.83mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-20-+60°C
Colour	Other
Bending strength	Flexible

Packaging

Outer Quantity	100
Outer Dimensions (inches)	20.75x20.38x8
Weight Uom	0.53 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000009
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website