



Catalog Number: LTBUS05L-E
Product ID: 7TAA012LFOR0014
UPC Number: 78621011180
EAN Number: 05415022393194
Status: A



Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 1-1/4 Inch, Length 60 Meters/200 Feet, For Computer Data Systems, UL 360, CSA, Compliant to RoHS, Working Temperature -20 to 60 Degrees C, Blue

Representative

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	1-1/4 in ; 40 mm
Outside Diameter	1.660 in
Inside Diameter	1.380 in
Length	200 ft ; 60 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Blue

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Outer diameter	42.16mm
Inner diameter	35.05mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-20-+60°C
Colour	Blue
Bending strength	Flexible

Packaging

Outer Quantity	200
Outer Dimensions (inches)	20x32x32
Weight Uom	1.02 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000009
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website